

# Dispensing Equipment Selection and Setup Considerations for Dual-Cure Materials

Dymax Dual-Cure systems are single-component, nonreactive, solvent-free adhesives and coatings that cure with UV/Visible light and moisture over time. Dual-Cure materials have a one-year shelf live when stored at room temperature in the sealed original container. Storage instructions for opened packages are on the original package. In addition, the following guidelines will help ensure a stable, consistent dispensing process.

# UTILIZE OPAQUE DISPENSING NEEDLES AND FLUID LINES

It is important that 100% light-blocking (not just UV blocking) dispensing needles and fluid lines are used when dispensing.

### **ENSURE COMPATIBLE WETTED COMPONENTS**

Dymax materials are readily dispensed through a wide variety of commercially available valves and pressure pots. When selecting a dispensing system, make sure that wetted components are compatible with Dymax materials. Incompatible wetted components can be attacked by Dymax materials or cause them to cure prematurely in dispensing equipment.

KNOWN COMPATIBLE MATERIALS	KNOWN INCOMPATIBLE MATERIALS
Acetels	Aluminum
Stainless Steel (300 series)	Brass
Hard Chrome	Bronze
HDPE, HDPP (opaque)	Cast Iron
Nylon (pure)	Copper
Silicone (opaque)	Magnetic Stainless Steel (400 series)
Teflon® (opaque)	Mild Steel
	N-Butyl "O" Rings
	Polyurethane
	Polycarbonate
	PVC
	Zinc

## **AVOID HIGH-SHEAR VALVES AND PUMPS**

Some Dymax materials are shear sensitive, meaning that high shear can initiate polymerization (curing). Shear occurs when material is caught between two tightly fitting moving metal parts. Dymax therefore does not recommend the use of pumps that cause high shear such as gear pumps (simple pressure pot, pneumatic systems, or ram-style pail pumps are typically adequate). Dymax does not recommend positive displacement dispensing valves unless testing shows they are compatible with the specific Dymax material involved. Contact Dymax Applications Engineering for further guidance in selecting an appropriate dispensing system.

# **UTILIZE "YELLOW LIGHTS" (IF NECESSARY)**

Some application techniques (i.e. roll coating and stencil/screen printing) require prolonged exposure to ambient lighting. Given enough time, standard fluorescent and incandescent lighting can initiate polymerization (curing) of some Dymax Dual-Cure materials. Special "yellow lighting" is available that will prevent this premature polymerization.

### RETROFIT LAMPS AVAILABLE FOR EXISTING FLUORESCENT AND INCANDESCENT FIXTURES:

LAMP TYPE	MFG.	MODEL #	CONFIGURATION
Fluorescent	Philips	F40GO	T-12 Bi Pin, 4'
Fluorescent	Philips	F48T12GO	T-12 Single Pin 4'
Fluorescent	Philips	F96T12GO	T-12 Single Pin 8'
Fluorescent	Philips	F96T12GO/HO	T-12 Dual Pin Raised Oval 8'
Fluorescent	GE	F32T8GO/CVG	T-8 Bi Pin, 4'
Incandescent	Sylvania	Bug Foiler, 60 watt	Medium base

# THE FOLLOWING COMPLETE LIGHT FIXTURE IS RECOMMENDED FOR NEW OR RETROFIT **INSTALLATIONS:**

Holophane Model # EN250HPXXP7; Type: High pressure sodium, high bay

# **Holophane Fixture Notes:**

- 1. XX denotes voltage (to be specified by customer).
- Because the main fixture normally takes up to 5 minutes to restart, an available quartz restrike option allows instant "walk around" lighting in the event of a temporary power failure. For this option, add suffix "EM".
- 3. Substitute LHP for HP in model number if energy-saving ballast is desired.
- 4. For hook, cord, and plug option, add Suffix #CDP-LX-15-3-PF121. No suffix denotes standard hard-wire configuration.
- Lamp Type: General Electric # GLU250/D. (Maximum wattage for this application is 250. Higher wattages have not been tested.)
- Holophane Factory Contact: Tom Quigley Phone (860) 621-9136.

### **BLANKET MOISTURE-SENSITIVE MATERIALS WITH INERT GAS**

Dymax Dual-Cure systems are sensitive to moisture in the uncured state. Prolonged exposure to moisture can cause Dymax Dual-Cure systems to polymerize. To avoid these effects, the materials should be stored in their original packaging or metal containers and blanketed with inert gas (i.e. nitrogen or argon) when re-sealed. Also, pressure pots containing these materials should be pressurized with an inert gas or dry air.

# ENSURE SOLVENTS USED FOR CLEAN UP AND PURGING FLUID LINES DO NOT CONTAIN MOISTURE:

Cleaning Dymax Dual-Cure systems in the uncured state is relatively simple as the material will dissolve in nonalcoholic solvents. Alcoholic solvents that contain moisture activate the curing process. Therefore, it is recommended that non-alcohols be used to clean up uncured material and purge wetted dispensing lines.

COMMON NON-ALCOHLIC SOLVENTS	COMMON ALCOHOLIC SOVENTS
Butyl Acetate	Propylene Glycol Monomethyl Ether (PM)
Acetone	2-Butoxyethanol
Methyl Ethyl Ketone (MEK)	Isopropyl Alcohol (IPA)
PM Acetate	Ethanol
2-Butoxyethyl Acetate	Methanol



@ 1998-2010 Dymax Corporation. All rights reserved. All trademarks in this bulletin, except where noted, are the property of, or used under license by Dymax Corporation, U.S.A.

The data contained in this bulletin is of a general nature and is based on laboratory test conditions. Dymax Europe GmbH does not warrant the data contained in this bulletin. Any warranty applicable to products, its application and use is strictly limited to that contained in Dymax Europe GmbH's General Terms and Conditions of Sale published on our homepage <a href="http://www.dymax.com/de/pdl/dymax.europe\_general\_terms\_and\_conditions\_of\_sale\_pdl">http://www.dymax.com/de/pdl/dymax.europe\_general\_terms\_and\_conditions\_of\_sale\_pdl</a>. Dymax Europe GmbH does not assume any responsibility for test or performance results obtained by users. It is the user's intended manufacturing apparatus and methods. The user should adopt such precautions and use guidelines as may be reasonably advisable or necessary for the protection of property and persons. Nothing in this bulletin shall act as a representation that the product use or application will not infininge a patent owned by someone other than Dymax Corporation or act as a grant of license under any Dymax Corporation Patent. Dymax Europe GmbH recommends that each user adequately test its proposed use and application of the products before actual repetitive use, using the data contained in this bulletin as a general guide. LIT136EU 3/28/2008

Dymax Corporation 860.482.1010 | info@dymax.com | www.dymax.com

**Dymax Europe GmbH** +49 (0) 611.962.7900 | info\_de@dymax.com | <u>www.dymax.de</u>

Dymax Engineering Adhesives Ireland Ltd. +353.1.231 4696 | info\_ie@dymax.com | www.dymax.com

Dymax Oligomers & Coatings 860.626.7006 | info\_oc@dymax.com | www.dymax-oc.com

Dymax UV Adhesives & Equipment (Shanghai) Co. Ltd.

Dymax UV Adhesives & Equipment (Shenzhen) Co. Ltd. +86.755.83485759 | dymaxasia@dymax.com | <u>www.dymax.com.cn</u>

Dymax Asia (H.K.) Limited +852.2460.7038 | dymaxasia@dymax.com | www.dymax.com.cn

Dymax Asia Pacific Pte. Ltd.

+65.6752.2887 | info\_ap@dymax.com | www.dymax-ap.com

Dymax Korea LLC

+82.2.784.3434 | info\_kr@dymax.com | www.dymax.com/kr