

- Precise dispensing control for wide variety of dot or deposit sizes
- Suitable for a large range of viscosities, and all types of fluids
- Manual and timer modes for precise control
- High cycle speed for automated dispensing operations
- 1 programmable memory slot for timing storage
- CE certified

SD-200 Digital Syringe Dispenser

The SD-200 digital liquid dispenser, with its versatile design, is perfectly suited for a wide variety of dispensing applications from microdot deposits to large potting and filling. Suitable for all types of fluids, it includes a suck-back feature to ensure low viscosity liquids do not drip from the dispense tip.

The SD-200 provides a micro-controlled timer programmable from 0.01 to 99.99 seconds. Operation can be in manual mode controlled by a foot pedal or with pre-set time for repeatable shot sizes. The unit comes with a programmable memory slot to store timing.

Included hoses, fittings, and dispense tips make the unit ready to use right out of the box. The SD-200 includes:

- SD-200 Digital Syringe Dispense Controller
- Adapter Assemblies: 3, 5, 10, and 30/55 CC
- Push to Connect Tube Fitting 1/4" Stem OD x 5/32" Tube OD with Tubing
- Foot Pedal
- Power Adapter with Attachments
- Syringe Stand
- Tip Kits: High and Low Viscosity
- User Manual

Special Features & Benefits



Feature	Benefit
Adjustable vacuum suck-back	Clean, drip-free cycle shut-off
Digital timer with a range of 0.01 to 99.99 seconds	Precision control over fluid dispense
Delivers micro-shots, beads, or fills	Timed or manual mode with adjustable time and pressure settings; includes the ability to save a set time in memory
Activation by foot pedal (footswitch) or external signal	Manual or system-integrated operation
Adjustable air pressure fluid regulator	Adjust and set the proper air pressure setting for very thin fluids to very thick fluids

Specifications

Power Requirements	Input Voltage: 100 - 240 VAC, 50 / 60 Hz Internal Voltage: 24 VDC
Air Requirements	Input: 100 psi [7 bar] max Output: 1 - 100 psi [0.07-7 bar]
Relative Humidity	20-90% (No Condensation)
Operating Temperature	50-104°F (10-40°C)
Dispense Time	0.01- 99.99 seconds
Cycle Speed	Up to 600 cycles /minute
Dimensions (W x D x H)	7.56" x 7.17" x 3.00" (192 mm x 182 mm x 76 mm)
Weight	2.14 lbs (0.97 kg)
Unit Warranty	1 year from purchase date



Ordering Information


Units are warrantied against defects in material and workmanship for one year from date of purchase.

Part Number	60600 SD-200 Syringe Dispenser*
Accessories	60742Foot Pedal60756Syringe Stand60743Power Adapter
Air Cap Assemblies	60589Adapter Assembly, 3 CC60592Adapter Assembly, 5 CC60591Adapter Assembly, 10 CC60590Adapter Assembly, 30/55 CC
Tip Kits	P3423 Tip Kit, High Viscosity P3424 Tip Kit, Low Viscosity T11182-10 Syringe Tip Cap T16972 Dispense Tip Kit (assorted)

* For customer in Europe, the appropriate power cord will be added.



Main Components of the SD-200 Syringe Dispenser





.....

Americas USA | +1.860.482.1010 | info@dymax.com

Europe

Germany | +49 611.962.7900 | info_de@dymax.com Ireland | +353 21.237.3016 | info_ie@dymax.com

©2020 Dymax Corporation. All rights reserved. All trademarks in this guide, except where noted, are the property of, or used under license by, Dymax Corporation, U.S.A.

Please note that most dispensing system applications are unique. Dynax does not warrant the fitness of the product for the intended application. Any warranty applicable to the product, its application and use is strictly limited to that contained in Dynax standard Conditions of Sale published on our website. Dynax recommends that any intended application be evaluated and tested by the user to ensure that desired performance criteria are satisfied. Dynax is willing to assist users in their performance testing and evaluation. Data sheets are available for valve controllers or pressure pots upon request. PB085DA 1/23/2020

Asia

Singapore | +65.67522887 | info_ap@dymax.com Shanghai | +86.21.37285759 | dymaxasia@dymax.com Shenzhen | +86.755.83485759 | dymaxasia@dymax.com Hong Kong | +852.2460.7038 | dymaxasia@dymax.com Korea | +82.31.608.3434 | info_kr@dymax.com